


NETZSCH

Proven Excellence.



MultiProtector: The Monitoring and Protection Unit

An app displays the critical data of your pump, warns, and protects it from damage

Pumps & Systems

MultiProtector

Pump protection device for NETZSCH pumps

The MultiProtector is a monitoring and protection unit developed for NETZSCH positive displacement pumps. With this device, you can detect possible pump difficulties at an early stage. Based on, preset threshold values, you can protect the pump from damage in advance.

The MultiProtector analyzes the data on overpressure, temperature, leakage (conductivity measurement) and voltage. In the "MultiProtector" app, you can define two threshold values. One threshold value causes an alarm, the second one triggers a warning, which can also be used to switch off the pump. In addition, the error history is documented, and a live diagnostic can be performed. You can analyze the condition of the pump based on individual reports and optimise it. The pump is thus protected from damage.

What can be monitored?

- Temperature of the motor, stator, and pumped medium
- Pressure at the discharge port of the pump, signal input 0-20 mA (4-24 mA)
- 2 ways to measure leakage (conductivity measurement)
- Motor frequency
- Motor voltage

With the "MultiProtector" app, handling is very easy

The MultiProtector pump protection unit can be connected to mobile devices such as smartphones, tablets or laptops. With the app, you can set the threshold values on the device, display the pump's sensor data in real-time and generate reports.



MultiProtector
Material No. 8064772

NETZSCH
www.netzsch.com

INT69® YF Diagnose
Part-No. 22A701P071 made by KRIWAN
Supply AC 50/60Hz 100-240V 9VA
T_a -30...+70°C
Relay AC 240V 2.5A C300


Configurable inputs	Terminals	Adjustable range
Line voltage 3 AC 20-100Hz	L1, L2, L3	100-690V
Motor temperature	T1, T2	Bimetal, PTC, P1000, P1100
Temperature 1	T3, T4	PTC, P1000, P1100
Temperature 2	T5, T6	PTC, P1000, P1100
Leakage 1	E1, E2	10k-15MΩ
Leakage 2	E3, E4	10k-15MΩ
Current input	In, I ₁	0-20mA

01292




001-01547 2 • Made in Germany

Installed in a control cabinet



Analyzer: MultiProtector



Real-time diagnosis



2 threshold values can be defined per sensor. These can lead to a warning signal or switch off the pump.




Sensor for motor voltage and temperature

Sensor for leakage detection

Sensor for monitoring the media temperature

Temperature sensor for dry-running protection


Sensor for measuring the discharge pressure of the pump



Anytime and anywhere

Retrieve data and avoid downtime

With one click in the app, you can create a PDF report with error history, statistics and set parameters. You can use this for documentation or also for troubleshooting.



NETZSCH Pumpen & Systeme GmbH · Geretsrieder Straße 1 · 84478 Waldkraiburg · Germany
Tel.: +49 8638 63-0 · info.nps@netzsch.com · www.netzsch.com